

# The Original Ultrasonic Brass Instrument Cleaner

## ...cleans in only 2 to 4 minutes

Why use the ultrasonic cleaning process?

- Environmentally friendly
- Replaces harmful acids and chemicals
- Prolongs life of instruments
- Cleans inside and out
- Cleans all types and sizes of instruments
- Stainless steel construction
- Portable design



Repair shops, manufacturers, universities and school districts world wide agree that UPC cleaners deliver expected results - clean instruments in less time without hazardous chemicals.

GENERATOR CERTIFICATIONS




A PROUD SUPPORTER OF NAPBIRT

[WWW.UPCORP.COM](http://WWW.UPCORP.COM)

	ALTO	
Capacity	24.9 Gallon	94.4 Liter
Internal Dimensions	24.0 "W x 24.0 "L x 12.0 "D / 610 mm x 610 mm x 305 mm	
External Dimensions	25.5 "W x 30.6 "L x 15.4 "D / 648 mm x 777 mm x 391 mm	
Ultrasonic Power (Avg/Peak)	750 Watts	1500 Watts
Input Voltage	120 VAC 50/60Hz	
Approx. Shipping Weight	185 lbs	83.9 kg

**Ultrasonic Power Corporation....more POWER to clean.**



# ULTRASONIC POWER CORPORATION

239 E. Stephenson Street . Freeport, IL USA 61032  
815-235-6020 . 800-575-0168 . FAX 815-232-2150

[WWW.UPCORP.COM](http://WWW.UPCORP.COM) . [sonic@upcorp.com](mailto:sonic@upcorp.com)



MADE IN THE U.S.A